CCTXE | IP6A-16LUTP-1LK08-BLUNT

Base Product



InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, dual row OneLink 2x4 to unterminated, 16 links

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Copper trunk cable assembly

Product Brand GigaSPEED X10D® | InstaPATCH® Cu

General Specifications

ANSI/TIA Category 6A

Cable Type U/UTP (unshielded)

Conductor Type Solid

Interface, Connector AOneLink 2x4Interface Feature, connector AStandard

Interface, Connector B Unterminated

Link Count 16

Wiring T568B

Dimensions

Cable Assembly Length Range (m) 2 - 30

Cable Assembly Length Range (ft) 7 - 98


Electrical Specifications

dc Resistance, maximum0.3 ohmSafety Voltage Rating300 V

Ordering Tree

COMMSCOPE®

CCTXE | IP6A-16LUTP-1LK08-BLUNT



Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Environmental Space Low Smoke Zero Halogen (LSZH)

Flammability Rating UL 94 V-0

Included Products

3095B-4/24 – GigaSPEED X10D® 3095B Category 6A U/UTP Cable, non-plenum, 4 pair count



3095B-4/24

GigaSPEED X10D® 3095B Category 6A U/UTP Cable, non-plenum, 4 pair count

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio SYSTIMAX®

 Product Type
 Twisted pair cable

 Product Brand
 GigaSPEED X10D®

General Specifications

Product Number 3095B
ANSI/TIA Category 6A

Cable Component Type Cordage

Cable TypeU/UTP (unshielded)

Conductor Type, singlesSolidConductors, quantity8Pairs, quantity4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D

Dimensions

 Diameter Over Jacket, nominal
 7.239 mm | 0.285 in


 Jacket Thickness
 1.524 mm | 0.06 in

Conductor Gauge, singles 24 AWG

Cross Section Drawing



3095B-4/24



Electrical Specifications

Characteristic Impedance100 ohmCharacteristic Impedance Tolerance±15 ohm

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 9.38 ohms/100 m | 2.859 ohms/100 ft

Dielectric Strength, minimum1500 Vac | 2500 VdcMutual Capacitance at Frequency6.0 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 67 %

Operating Frequency, maximum 550 MHz

Remote PoweringFully complies with the recommendations set forth by IEEE 802.3bt (Type

4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA

TSB-184-A

Safety Voltage Rating 300 V

Material Specifications

Conductor Material Bare copper

COMMSCOPE®

3095B-4/24

Insulation Material Polyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Separator MaterialPolyolefinSeparator 2 MaterialPolyolefin

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature $0 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature -20 °C to +60 °C (-4 °F to +140 °F)

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-3-22
Smoke Test Method IEC 61034-2

Packaging and Weights

Cable weight 52.741 kg/km | 35.44 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

