

# APT-HFHM

---



Quarterwave Surge Arrestor 695-2700MHz, with interface types 4.3-10 Female and 4.3-10 Male

## Product Classification

**Product Type** Surge arrestor

## General Specifications

**Device Type** dc Pass

**Inner Contact Plating** Silver

**Interface** 4.3-10 Female

**Interface 2** 4.3-10 Male

**Outer Contact Plating** Trimetal

## Dimensions


**Height** 73 mm | 2.874 in

**Width** 25 mm | 0.984 in

**Length** 97 mm | 3.819 in

## Outline Drawing

# APT-HFHM



## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Gain</b>               | -117 dB              |
| <b>3rd Order IMD Test Method</b>        | Two +43 dBm carriers |
| <b>Insertion Loss, typical</b>          | 0.08 dB              |
| <b>Connector Impedance</b>              | 50 ohm               |
| <b>Lightning Surge Current</b>          | 10 kA                |
| <b>Lightning Surge Current Waveform</b> | 8/20 waveform        |
| <b>Operating Frequency Band</b>         | 695 – 2700 MHz       |
| <b>Peak Instantaneous Power (PIP)</b>   | 150 kW RF            |

## VSWR/Return Loss

| Frequency Band       | VSWR | Return Loss (dB) |
|----------------------|------|------------------|
| <b>695–806 MHz</b>   | 1.25 | 19.1             |
| <b>806–2170 MHz</b>  | 1.13 | 24.3             |
| <b>2170–2600 MHz</b> | 1.15 | 23.13            |

## Mechanical Specifications

|  |                           |
|--|---------------------------|
| <b>Coupling Nut Proof Torque</b>           | 10 N-m   88.507 in lb     |
| <b>Coupling Nut Retention Force</b>        | 449.27 N   101 lbf        |
| <b>Coupling Nut Retention Force Method</b> | MIL-C-39012C-3.25, 4.6.22 |

# APT-HFHM

---

|                                     |   |
|-------------------------------------|---|
| <b>Interface Durability</b>         | 100 cycles                                  |
| <b>Interface Durability Method</b>  | IEC 61169-16:9.5                            |
| <b>Mechanical Shock Test Method</b> | MIL-STD-202F, Method 213B, Test Condition C |

## Environmental Specifications

|   |   |
|---|---|
| <b>Operating Temperature</b>              | -45 °C to +85 °C (-49 °F to +185 °F)                                |
| <b>Storage Temperature</b>                | -70 °C to +150 °C (-94 °F to +302 °F)                               |
| <b>Attenuation, Ambient Temperature</b>   | 20 °C   68 °F   |
| <b>Average Power, Ambient Temperature</b> | 40 °C   104 °F  |
| <b>Corrosion Test Method</b>              | MIL-STD-202, Method 101, Test Condition B                           |
| <b>Immersion Depth</b>                    | 1 m   |
| <b>Immersion Test Mating</b>              | Mated   |
| <b>Immersion Test Method</b>              | IEC 60529:2001, IP68  |
| <b>Moisture Resistance Test Method</b>    | MIL-STD-202, Method 106   |
| <b>Thermal Shock Test Method</b>          | MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C |
| <b>Water Jetting Test Mating</b>          | Mated   |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |



## \* Footnotes

|                                |   |
|--------------------------------|---|
| <b>Insertion Loss, typical</b> | 0.05√freq (GHz) (not applicable for elliptical waveguide) |
| <b>Immersion Depth</b>         | Immersion at specified depth for 24 hours                 |