

# DB586-XT



1-port omni antenna, 806–869 MHz, 360° HPBW, fixed electrical tilt, fits on 38–51 mm (1-1/2 to 2 in) OD pipe

- Light weight, low profile omnidirectional antenna ideal for low to moderate gain applications
- Integral dual purpose mount allows top or side mounting

## OBSOLETE

This product was discontinued on: March 31, 2021

## General Specifications

<b>Antenna Type</b>	Omni
<b>Band</b>	Single band
<b>Color</b>	Horizon blue
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Performance Note</b>	Outdoor usage
<b>Radome Material</b>	Fiberglass, UV resistant
<b>Radiator Material</b>	Brass
<b>RF Connector Interface</b>	N Female
<b>RF Connector Location</b>	Bottom
<b>RF Connector Quantity, high band</b>	0
<b>RF Connector Quantity, mid band</b>	0
<b>RF Connector Quantity, low band</b>	1
<b>RF Connector Quantity, total</b>	1

## Dimensions

<b>Length</b>	1,498.6 mm   59 in
<b>Net Weight, without mounting kit</b>	3.6 kg   7.937 lb
<b>Outer Diameter</b>	38.1 mm   1.5 in

## Electrical Specifications

<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	806 – 869 MHz

# DB586-XT

---

**Polarization** Vertical

## Electrical Specifications

<b>Frequency Band, MHz</b>	<b>806–869</b>
<b>Gain, dBi</b>	8.1
<b>Beamwidth, Horizontal, degrees</b>	360
<b>Beamwidth, Vertical, degrees</b>	18
<b>Beam Tilt, degrees</b>	0
<b>VSWR   Return loss, dB</b>	1.5   14.0
<b>PIM, 5th Order, 2 x 20 W, dBc</b>	-153
<b>Input Power per Port, maximum, watts</b>	400

## Mechanical Specifications

<b>Wind Loading @ Velocity, maximum</b>	89.4 N @ 100 mph (20.1 lbf @ 100 mph)
<b>Wind Speed, maximum</b>	201 km/h (125 mph)

## Packaging and Weights

**Included** V-bolts

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance