

F1R-NRDF-2M5-P



FSJ1RK-50B SureFlex® Jumper with interface types N Male Right Angle and 7-16 DIN Female, 2.5 m

Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Brand | HELIAX® SureFlex® |
| Product Series | FSJ1-50B |

General Specifications

| | |
|---|-----------------|
| Body Style, Connector A | Right angle |
| Body Style, Connector B | Straight |
| Interface, Connector A | N Male |
| Interface, Connector B | 7-16 DIN Female |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 2.5 m 8.202 ft |
| Nominal Size | 1/4 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -107 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 680–960 MHz | 1.152 | 23.02 |
| 1700–2200 MHz | 1.152 | 23.02 |
| 2200–2700 MHz | 1.152 | 23.02 |

Jumper Assembly Sample Label

F1R-NRDF-2M5-P



Environmental Specifications

| | |
|--|---|
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d0 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Immersion Test Method | Meets IEC 60529:2001, IP68 in mated condition |