

RRV4-65C-R6



12-port sector antenna, 4x 694–960 and 8x 1695–2690 MHz, 65° HPBW, 6x RET.

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	8
RF Connector Quantity, low band	4
RF Connector Quantity, total	12

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male
Input Voltage	10–30 Vdc
Internal RET	Low band (2) Mid band (4)
Power Consumption, active state, maximum	8 W
Power Consumption, idle state, maximum	1 W
Protocol	3GPP/AISG 2.0

Dimensions

RRV4-65C-R6

Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	2438 mm 95.984 in
Net Weight, antenna only	46.3 kg 102.074 lb

Array Layout

Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	694-960	1-2	1	CPxxxxxxxxxxxxxxxxR1
R2	694-960	3-4	2	CPxxxxxxxxxxxxxxxxR2
Y1	1695-2690	5-6	3	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	7-8	4	CPxxxxxxxxxxxxxxxxY2
Y3	1695-2690	9-10	5	CPxxxxxxxxxxxxxxxxY3
Y4	1695-2690	11-12	6	CPxxxxxxxxxxxxxxxxY4

Left Bottom Right

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

RRV4-65C-R6



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	698–806	790–896	890–960	1695–1990	1920–2300	2300–2500	2490–2690
Beamwidth, Horizontal, degrees	71	70	65	60	61	60	65
Beamwidth, Vertical, degrees	9.7	8.8	8.2	7.7	6.9	6.1	5.8
Beam Tilt, degrees	2–12	2–12	2–12	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	20	18	16	18	18	18	17
Front-to-Back Ratio at 180°, dB	33	35	34	37	38	35	33
Front-to-Back Total Power at 180° ± 30°, dB	20	22	24	31	29	28	27
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25

RRV4-65C-R6

VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	300	300	300	250	250	250	200

Electrical Specifications, BASTA

Frequency Band, MHz	698-806	790-896	890-960	1695-1990	1920-2300	2300-2500	2490-2690
Gain by all Beam Tilts, average, dBi	15.1	15.5	15.7	16.6	17.2	17.4	16.9
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.5	±0.4	±0.8	±0.7	±0.7	±0.7
Beamwidth, Horizontal Tolerance, degrees	±3.5	±4.3	±5	±3.6	±3.3	±5	±5.6
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.6	±0.5	±0.5	±0.6	±0.3	±0.3
USLS, beampeak to 20° above beampeak, dB	16	15	5	15	15	14	13
CPR at Boresight, dB	25	25	25	20	21	17	15
CPR at Sector, dB	7	6	9	10	8	8	6

Mechanical Specifications

Wind Loading @ Velocity, frontal	948.0 N @ 150 km/h (213.1 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	305.0 N @ 150 km/h (68.6 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,331.0 N @ 150 km/h (299.2 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	751.0 N @ 150 km/h (168.8 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	309 mm 12.165 in
Length, packed	2685 mm 105.709 in
Weight, gross	66.2 kg 145.946 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

RRV4-65C-R6

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted



Included Products

- | | | |
|----------|---|--|
| BSAMNT-3 | - | Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set. |
| BSAMNT-M | - | Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set. |

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance