

252SE

Fixed-tuned CPR137G for elliptical waveguide 52

Product Classification

Product Type Elliptical waveguide connector

General Specifications

Attachment Method Tab-flare | Tool-flare

Body Style Straight, fixed-tuned

Inner Contact Plating Unplated

Interface CPR137G

Outer Contact Plating Unplated

Pressurizable Yes

Dimensions

Width 88.9 mm | 3.5 in

Length 114.554 mm | 4.51 in

Transition Length 75.692 mm | 2.98 in

Waveguide Size WR137 | WG14 | R70

Electrical Specifications

Insertion Loss, typical 0.01 dB

Operating Frequency Band 5.0 – 6.425 GHz

Peak Power at Frequency, maximum 92.00 kW @ 6.00 GHz

Material Specifications

Material Type Brass

Environmental Specifications

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Packaging and Weights

Weight, net 1.8 kg | 3.968 lb

252SE

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant



* Footnotes

Insertion Loss, typical 0.05v̄freq (GHz) (not applicable for elliptical waveguide)