

A60450-000 | OC-ADP-E9-E9-NNCS-AC

Fiber Optic Simplex Adapter, Singlemode LSH/APC, green, flanged

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

OBSOLETE

This product was discontinued on: October 23, 2020

Replaced By:

760249514 Fiber Optic Simplex Adapter, Singlemode LSH/APC, green, flanged
OC-ADP-EC-EC-NNCS-AL

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Fiber adapter
Product Series	OC-ADP

General Specifications

Body Style	Simplex
Color	Green
Interface	LSH/APC
Mounting	Square flange
Total Ports, quantity	1
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Material Specifications

Alignment Sleeve Material	Ceramic
---------------------------	---------

Mechanical Specifications

Coupling Retention Force	70 N 15.737 lbf
--------------------------	-------------------

Optical Specifications

Fiber Mode	Singlemode
Insertion Loss, maximum	0.1 dB

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity 1

Packaging Type Bag

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

