

# F4A-HMDR-3M-P



HELIAX® 1/2" Superflexible SureFlex® Jumper with interface types 4.3-10 male and 7-16 DIN right angle male, 3 m

## Product Classification

|                       |                               |
|-----------------------|-------------------------------|
| <b>Product Type</b>   | SureFlex® Premium, static PIM |
| <b>Product Brand</b>  | HELIAX®   SureFlex®           |
| <b>Product Series</b> | RSJ4-50                       |

## General Specifications

|   |               |
|---|---------------|
| <b>Body Style, Connector A</b>            | Straight      |
| <b>Body Style, Connector B</b>            | Right angle   |
| <b>Interface, Connector A</b>             | 4.3-10 Male   |
| <b>Interface, Connector B</b>             | 7-16 DIN Male |
| <b>Specification Sheet Revision Level</b> | B             |

## Dimensions

|                     |                |
|---------------------|----------------|
| <b>Length</b>       | 3 m   9.843 ft |
| <b>Nominal Size</b> | 1/2 in         |

## Electrical Specifications

|   |                      |
|---|----------------------|
| <b>3rd Order IMD Static</b>             | -116 dBm             |
| <b>3rd Order IMD Static Test Method</b> | Two +43 dBm carriers |
| <b>DTF, Connector A</b>                 | -34 dB               |
| <b>DTF, Connector B</b>                 | -32 dB               |

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 698–970 MHz    | 1.083 | 28               |
| 1700–2200 MHz  | 1.083 | 28               |
| 2200–2700 MHz  | 1.135 | 24               |
| 3400–3800 MHz  | 1.222 | 20               |

# F4A-HMDR-3M-P

## Jumper Assembly Sample Label



## Environmental Specifications

### Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

## Regulatory Compliance/Certifications

### Agency

### Classification

|               |  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

