

PFP-SPS-1600M



Slimline SPS DC Rectifier Module, 1600 Watts

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type

Power supply module

Dimensions

Height

41.656 mm | 1.64 in

Width

126.492 mm | 4.98 in

Depth

205.994 mm | 8.11 in

Electrical Specifications

Input Current Range

15-12A @ 90-120Vac | 7.5A @ 230Vac

Output Voltage Range

-42 to -58 Vdc

Electrical Safety Standard

CE | CSA C22.2 No. 60950-1-03 | UL

Electromagnetic Compatibility/Interference (EMC/EMI)

FCC-CFR, Part 15, sub-part B | GR1089 Class A

Power Efficiency

95 %

Environmental Specifications

Operating Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Standards Compliance

EN 61000-4-2 level 4 | GR 1089, Issue 4 | GR-63

Packaging and Weights

Packaging quantity

1

Packaging Type

Carton

Weight, net

1.397 kg | 3.08 lb

PFP-SPS-1600M

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

