

ATCB-DB9-016

RET control cable 16m with male DB9 and female AISG connector



- Feeds data and power to RET system components
- Directly connects RET actuator with RRH (Remote Radio Heads) with DB9 connector

OBSOLETE

This product was discontinued on: May 31, 2016

Replaced By:

ATCB-DB9-020

RET control cable 20m with male DB9 and female AISG connector

Product Classification

Product Type AISG DB9 cable

General Specifications

AISG Connector A	8-pin DIN Female
AISG Connector A Body Style	Straight
AISG Connector A Standard	IEC 60130-9
Color	Black
Connector B	9-pin D-sub Male
Data Conductor Type	0.24 mm ² (24 AWG) twisted pair
EU Certification	CB CE
Power Conductor Type	0.82 mm ² (18 AWG) stranded

Dimensions

Length	16 m 52.493 ft
Diameter Over Jacket	8 mm 0.315 in

Electrical Specifications

Protocol	AISG 1.1 AISG 2.0
Voltage, maximum	300 V

ATCB-DB9-016

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 100%
Climatic Sequence Test Method	IEC 60068-2-14
Corrosion Test Method	IEC 60068-2-11, Test Condition Ka
Ingress Protection Test Method	IEC 60529:2001, IP67
UV Resistance Test Method	IEC 60068-2-5, Test Condition B

Packaging and Weights

Weight, net	1.8 kg 3.968 lb
--------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
AISG	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

