



Fiber indoor cable, Low Smoke Zero Halogen Distribution, 12 fiber single-unit, Multimode OM4, Meters jacket marking, Aqua jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	N-DS

General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Aqua
Jacket Marking	Meters
Total Fiber Count	12

Dimensions

Diameter Over Jacket	6.2 mm 0.244 in
-----------------------------	-------------------

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	124 mm 4.882 in
Minimum Bend Radius, unloaded	62 mm 2.441 in
Tensile Load, long term, maximum	198 N 44.512 lbf
Tensile Load, short term, maximum	667 N 149.948 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1 E3
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

Fiber Type	OM4
-------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1,300 nm 3.00 dB/km @ 850 nm
-----------------------------	---

Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Flame Test Listing	NEC OFNR (UL) and c(UL)
Flame Test Method	IEC 60332-3 UL 1666 UL 1685

Environmental Test Specifications

Temperature Cycle Test Method IEC 60794-1 F1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5X-TB-3.0/1.0/093 – OM4 Bend-Insensitive Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable