Instruction Sheet

D701-0005 Revision F, October 2016

Multi-Beam Panel Antenna 5NPX1006F

General

This instruction sheet contains all necessary information required to assist in the correct installation of CommScope Multi-Beam Panel Antennas.

The following symbols can be found next to text outlining important information.



Please follow the procedure marked with this symbol precisely. Non-compliance may lead to damage of the product.



Handy tips when installing product.

Unpacking



To make sure no pressure and load on the radome of this antenna in handling and fixing.

Make sure that the antenna and the accessory items listed below are provided and have not been damaged during transport.

- Antenna
- Mounting kit
- Installation Instructions (This document)

Mounting Kits	Туре
Fixed Downtilt	F-042-GL-E
Mechanical Downtilt	T-045-GL-E



Do not install near power lines. Power lines, telephone lines, and guy wires look the same. Assume any wire or line can electrocute you.



Do not install on a wet or windy day or when lightning or thunder is in the area. Do not use metal ladder.



Wear shoes with rubber soles and heels. Wear protective clothing including a long-sleeved shirt and rubber gloves.



Installation Instructions



- Ensure a torque spanner is used when tightening fasteners, see the mounting kit diagrams on the following pages for the correct torque recommendations.
- Ensure antenna is installed with the connectors and drainage holes at the bottom.

Installation Instructions - Fixed Downtilt Mounting Kit (F-042-GL-E)

Assemble both mounting brackets to the antenna as per Figures 1, 2 & 3 of this document.



Attach the mounting kit assembly to the antenna, before trying to clamp the brackets to the pole.



The clamp brackets can clamp pipe diameters between 60mm (2.4") & 115mm (4.5"). For typical installations the minimum recommended pipe diameter is 75mm (3").

Figure 1. Correctly Assembled **Mounting Brackets**






Figure 2. Fixed Downtilt Mounting Bracket Assembled to Antenna & pole




Figure 3. Fixed Downtilt Mounting Bracket Exploded Assembly

Instruction Sheet

Installation Instructions - Mechanically Adjustable Downtilt Mounting Kit (T-045-GL-E), Bracket Spacing 716mm (28.2")


Assemble both mounting brackets as per Figures 4 and 5 (or Figures 7 and 8) of this document.




- 1. Attach the lower and upper mounting bracket assemblies to the antenna, before clamping the brackets to the pole. Downtilt angles of 0° and 2° to 10° in 1° increments can be obtained with the correct setting of the tilt arm bracket. For 0° downtilt the tilt arm may be stowed as show in Figure 5.
- 2. 2°-10° downtilt can be achieved by aligning the corresponding hole in the tilt arm to the pivot bracket which mates against the mounting pole, as shown in Figure 6 or Figure 9. The first hole is for 2° downtilt, with each consecutive hole resulting in an increased inclination of 1°.
- 3. When the tilt arm is used in the upper antenna bracket as shown in Figures 4 and 5, the mechanical tilt can be set to 0 ° or to any angle from 2 ° to 10 ° in 1 ° steps. The electrical beams emerge from the front of the antenna with a 6 ° electrical downtilt so 6° needs to be added to the mechanical tilt to find the actual pointing of the beams.
- 4. When the tilt arm is used in the lower mounting bracket as shown in Figure 6, the mechanical uptilt can be set to 0° or to any angle from 2° to 10° in 1° steps. The electrical beams emerge from the front of the antenna with a 6 ° electrical downtilt so the mechanical uptilt needs to be subtracted from the 6° electrical downtilt to find the actual downtilt of the beams.



The clamp brackets can clamp pipe diameters between 60mm (2.4") & 115mm (4.5"). For typical installations the minimum recommended pipe diameter is 75mm (3").








Figure 4 Arrangement of mounting kits to provide downtilt (details A and B in Figure 5)




Figure 5. Setting mechanical downtilt




Figure 6 Setting uptilt

Labelling of Antenna Beams

This antenna radiates 5 beams. As mentioned in connection with tilting of the antenna, the beams point downwards relative to the front face of the antenna at an angle of 6°. In the horizontal plane, the beams are at azimuth angles of -40° (i.e. 40° to the left of boresight when looking at the antenna from the rear), -20°, 0°, +20°, +40° (i.e. 40° to the right of boresight when looking at the antenna from the rear). There are 10 connectors to the antenna, one for each beam of the antenna at a polarization of +45° and one for each beam at a polarization of -45°.

The pairs of connectors for each beam direction are shown in Figure 7.



The labelling metioned here are not applyable for the antennas series number are, 00000001,00000002,00000003,00000004.




Figure 7 Arrangement of connectors on the base of the antenna.

Operation of Antennas

RF Cable Connection



The 7-16 female connectors fitted to the antenna are designed to fit jumper cables with a standard 7-16 RF male connector. After ensuring both mating connectors are dry push the male connector in and tighten the connector coupling to 23 - 28Nm (17 -21 ft.lb).

If needed or as required by local procedures a weatherproofing kit may then be fitted to the connection.

If the RF connectors are tightened beyond the recommend torque the RF connection to the antenna may be damaged.

Instruction Sheet

Revision	Changes	Date
A	First Release	2011-05-10
В	Add caution in content of unpacking	2013-03-26
С	More clearly define the recommended installation	2013-06-19
	requirements and warnings & update the figure 2 and 7.	
D	Changed drawing template to COMMSCOPE.	2013-07-25
Е	Update with latest CommScope template	2016-09-05
F	Replace "Argus" with "CommScope".	2016-10-31