

4672004/10 | UH68120 BLRL QD6/CAT6 1000



Siamese RG 6 Type Quad Shield w/ Category 6 Twisted Pair Non-Plenum Cable, blue jacket, 1000 ft (305 m) reel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, coax and twisted pair
Product Brand	UltraHome®

General Specifications

Product Number	UH68120
ANSI/TIA Category	6
Cable Type	Hybrid
Center Conductor Type	Solid
Construction Type	Non-armored
Jacket Color	Blue

Dimensions

Overall Cable Width	14.529 mm 0.572 in
Cable Length	304.8 m 1000 ft
Diameter Over Center Conductor Tolerance	±0.0004 in
Diameter Over Center Conductor, specific	0.0403 in per 1 strand
Diameter Over Conductor, singles, specific	0.0254 in per 1 strand
Diameter Over Dielectric	4.572 mm 0.18 in
Diameter Over Dielectric Tolerance	±0.004 in
Diameter Over Outer Shield (Braid)	5.893 mm 0.232 in
Center Conductor Gauge	18 AWG
Inner Shield (Braid) Gauge	34 AWG
Outer Shield (Braid) Gauge	34 AWG

4672004/10 | UH68120 BLRL QD6/CAT6 1000

Dimensions, Coaxial

Jacket Thickness	0.813 mm 0.032 in
Jacket Thickness, minimum spot	0.61 mm 0.024 in
Diameter Over Jacket	7.544 mm 0.297 in
Diameter Over Jacket Tolerance	±0.008 in

Electrical Specifications

Capacitance	52.493 pF/m 16 pF/ft
Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
Conductor dc Resistance	21.325 ohms/km 6.5 ohms/kft
Dielectric Strength, conductor to shield	2500 Vdc
Jacket Spark Test Voltage	4000 Vac
Nominal Velocity of Propagation (NVP)	82 %
Shield dc Resistance	16.076 ohms/km 4.9 ohms/kft
Structural Return Loss	15 dB @ 5–2200 MHz
Structural Return Loss Test Method	100% Swept Tested

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
1.0	1.21	0.37
10.0	2.16	0.66
50.0	4.62	1.41
100.0	6.3	1.92
200.0	8.66	2.64
400.0	12.23	3.73
700.0	16.56	5.05
900.0	18.99	5.79
1000.0	20.04	6.11
1200.0	22.07	6.73
1450.0	24.57	7.49
1800.0	27.65	8.43
2200.0	30.67	9.35
2500.0	32.7	9.97

3000.0

35.82

10.92

Material Specifications

Center Conductor Material	Bare copper
Conductor Material	Bare copper
Dielectric Material	Foam PE
Jacket Material	PVC
Inner Shield (Braid) Coverage	60 %
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Poly, bonded
Outer Shield (Braid) Coverage	40 %
Outer Shield (Braid) Material	Aluminum
Outer Shield (Tape) Material	Aluminum/Poly, non-bonded
Ripcord Material	Polypropylene

Mechanical Specifications

Minimum Bend Radius, loaded, times	20 times
Minimum Bend Radius, unloaded, times	10 times

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Non-plenum
Temperature Rating, UL	60 °C 140 °F
Flame Test Method	CM
Safety Standard	ETL cETL

Packaging and Weights

Cable weight	89.29 kg/km 60 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

4672004/10 | UH68120 BLRL QD6/CAT6 1000

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable