

## FEATURES

- Dual Density 1550 nm ITU DWDM return path transmitters
- High density allows 20 modules per chassis and 400 per 40RU rack
- Simplified installation and management with graphical user interface
- Universal management through Craft interface and SNMP with HMS

CommScope CHP Max5000® Dual Density Return Transmitters are an integral part of return path system applications allowing for more efficient use of optical headend rack space. Advanced two-way services—such as high-speed Internet access and telephony—require superior return path delivery capacity and performance. CHP Max5000 Converged Headend Platform can help you meet these demands.

The 2RU CHP Max5000 chassis can accommodate up to 10 dual density return transmitters (up to 400 transmitters in one standard 6-foot rack) to relieve the pressure on precious headend space as you expand offering of advanced two-way services.

CHP Max5000 Dual Density Return Transmitters are available for 16 DWDM ITU channels in the 1550 nm spectrum—all of which transmit in the 5 to 300 MHz spectrum and offer 60 dB of isolation between transmitters.



Longer distances can be achieved when using the CHP 1550 ITU Return Transmitter with the CHP Max5000 EDFA series modules, which simplifies applications by providing low noise, integrated element management capability, reduced rack space, and power requirements providing both CAPEX and OPEX savings.

CHP Max5000 Dual Density Return Path Transmitters offer hot-swapping and integrated monitoring and configuration control through a Craft graphical user interface with local or remote access. Remote management is accessible through the SNMP HMS-compliant interface for external connection to an element manager. Energy efficient internal components and effective thermal design keep lasers cool to ensure for effective, reliable performance.

Additional features include:

- High density return path solution with reduced heating, cooling, and power costs
- High 60 dB isolation between transmitters
- Front-panel RF test point for convenient monitoring
- Local or remote monitoring and configuration control using the Craft GUI
- Downloadable firmware upgrades

## WAVELENGTHS SUPPORTED

First	Second
21	23
25	27
29	31
33	35
43	45
47	49
51	53
55	57

## SPECIFICATIONS

Characteristics	Specification
<b>Physical</b>	
Dimensions <sup>1</sup>	1.25 in W x 3.4 in H x 18.5 in D (3.2 cm x 8.7 cm x 47.0 cm)
Weight	2.75 lb (1.24 kg)
RF Connector	F Type
Optical Connector	SC/APC
<b>Environmental</b>	
Operating Temperature Range <sup>2</sup>	0° to 50°C (32° to 122°F)
Storage Temperature Range	-40° to 70°C (-40° to 158°F)
Humidity	85% non-condensing (max)
<b>Optical</b>	
Wavelength	1531.9 to 1560.61 nm, specific channels in configurator
Wavelength Drift	0.15 nm (max)
Output Power	10 ± 0.25 dBm
<b>RF</b>	
Bandwidth	5 to 300 MHz
Input Impedance	75 Ω
Frequency Flatness, 25°C (77°F), Typical	± 0.5 dB
Input Return Loss	16 dB
RF Input Test Point, 25°C (77°F) <sup>3</sup>	-20 ± 0.75 dB
Port-to-Port Isolation	> 60 dB
Unit-to-Unit Isolation	> 65 dB
Port-to-Port Gain Variation	± 1.0 dB
<b>Performance</b>	
Total Input RF Power, Nominal	9 to 12 dBmV (OMI = 6% at input power of 0 dBmV/ch)
Noise-Power Ratio (NPR)/Dynamic Range	40/12 dB (35 km fiber with -7 dBm into RX), with 5–65 MHz loading 40/11 dB (35 km fiber with -7 dBm into RX) with 5–85 MHz loading 40/8 dB (35 km fiber with -7 dBm into RX) with 5–200 MHz loading
PIN Attenuation Range	4 dB
<b>Power Requirements</b>	
Power Consumption	18 W (max)

### NOTES:

1. Includes handles and connectors.
2. Temperature measured at transmitter's air inlet.
3. Relative to main port.

## ORDERING INFORMATION

				1	2	3	4		5	6	7	8		9	10		11
C	H	P	-	R	D	F	0	-	x	x	x	x	-	z	z	-	c
<b>1</b>	<b>Description</b>																
R	Return TX																
<b>2</b>	<b>Description</b>																
D	Dual Density																
<b>3</b>	<b>Description</b>																
F	Front Fiber																
W	Rear Fiber																
<b>4</b>	<b>Description</b>																
0	Fixed Output/Fixed Wavelength																
<b>5</b>	<b>6</b>	<b>7</b>	<b>8</b>	<b>Description</b>													
y	y	y	y	ITU Grid channel number pairings as listed below.													
				Laser 1 Channel							Laser 2 Channel						
21	23			21							23						
25	27			25							27						
29	31			29							31						
33	35			33							35						
43	45			43							45						
47	49			47							49						
51	53			51							53						
55	57			55							57						
<b>9</b>	<b>10</b>	<b>Description</b>															
1	0	10 dB Laser Output Power															
<b>11</b>	<b>Description</b>																
S	SC/APC Connector (Front Only Option)																
L	LC/APC Connector (Rear Only Option)																

## RELATED PRODUCTS

CHP Chassis	Optical Patch Cords
CHP Power Supplies	Optical Passives
CHP Management Module	Installation Services

Contact Customer Care for product information and sales:

- United States: 866-36-ARRIS
- International: +1-678-473-5656

**COMMScope®**

**Note:** Specifications are subject to change without notice.

**Copyright Statement:** © 2022 CommScope, Inc. All rights reserved. ARRIS, the ARRIS logo, and CHP Max5000 are trademarks of CommScope, Inc. and/or its affiliates. All other trademarks are the property of their respective owners. No part of this content may be reproduced in any form or by any means or used to make any derivative work (such as translation, transformation, or adaptation) without written permission from CommScope, Inc and/or its affiliates ("CommScope"). CommScope reserves the right to revise or change this content from time to time without obligation on the part of CommScope to provide notification of such revision or change.

1514637\_CHP-RDF0\_05\_RevA