


3399105 | 125T(TD)135WP1250TAPE



Toneable ConQuest® Empty Conduit, 1 1/4 in, SDR 13.5, terracotta, with pull tape

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Terracotta
Conductor Elongation, maximum	30 %
Conductor Type	Solid
Conduit Type	Toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	914.4 m 3000 ft
Conductor Diameter	1.024 mm 0.04 in
Inner Diameter, nominal	35.408 mm 1.394 in
Outer Diameter, nominal	42.164 mm 1.66 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	3.124 mm 0.123 in
Nominal Size	1-1/4 in
Conductor Gauge	18 AWG

Electrical Specifications

Conductor Resistance	98.425 ohms/km 30 ohms/kft
-----------------------------	------------------------------

3399105 | 125T(TD)135WP1250TAPE

Material Specifications

Conductor Material Type	Copper-clad steel (CCS)
Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE) Polyester
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	457.2 mm 18 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm ² 3000 psi
Breaking Strength	566.99 kg 1250 lb
Conductor Tensile Strength, minimum	344.738 N/mm ² 50000 psi
Pull Line Type	Tape
Pulling Tension Note	Applies to products manufactured after December 31, 2012
Pulling Tension, maximum	571.526 kg 1260 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net	394.363 kg/km 265 lb/kft
--------------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance