376744-000 | OCC1C-B-43A-NNSEC-C01



OCC1C compact CWDM, 8 channels + upgrade port, single demux, 1431 nm starting wavelength, 0.9 mm cable

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type CWDM component

Product Series OCC1C

General Specifications

Device Type Component, rectangular

Functionality Demultiplexing

Technology Type Free space optics

Application For use in FOSC closures

Circuits, quantity 1

Distribution Type 8-channel CWDM

Interface, InputStub tailInterface, OutputStub tail

Multiplexers, quantity 1

Port Type, optional Upgrade port

Dimensions

Pigtail Length, Input2.5 m | 8.202 ftPigtail Length, Output2.5 m | 8.202 ftPigtail Diameter0.9 mm | 0.035 in

Optical Specifications

Channel Spacing Skipped channels

Starting Wavelength 1431 nm

COMMSCOPE®

376744-000 | OCC1C-B-43A-NNSEC-C01

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



