

# C-30-UW-N-A16



30 dB, Air Directional Coupler, 555–6000 MHz

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Product Type	Directional coupler

## General Specifications

Device Type	Coupler
Application	Indoor/Outdoor
Color	Silver
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal

## Dimensions

Height	22 mm   0.866 in
Width	72 mm   2.835 in
Length	159 mm   6.26 in

## Electrical Specifications

3rd Order IMD	-163 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.2 dB @ 555–6000 MHz
Average Power, maximum	200 W
Coupling	30 dB
Coupling Tolerance	±1.5dB
Impedance	50 ohm
Isolation at Frequency Band	36 dB @ 4900–6000 MHz   42 dB @ 3800–4900 MHz   44 dB @ 2700–3800 MHz   46 dB @ 555–2700 MHz
Operating Frequency Band	555 – 6000 MHz

# C-30-UW-N-A16

Peak Power, maximum	1 kW
Reflected Power, maximum	200 W
VSWR at Frequency Band	1.25:1 @ 2700–3800 MHz   1.2:1 @ 555–2700 MHz   1.3:1 @ 3800–6000 MHz

## Mechanical Specifications

Coupling Nut Proof Torque	4.5 N-m   39.828 in lb
---------------------------	------------------------

## Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

## Packaging and Weights

Height, packed	45 mm   1.772 in
Width, packed	98 mm   3.858 in
Length, packed	180 mm   7.087 in
Weight, gross	0.44 kg   0.97 lb
Weight, net	0.38 kg   0.838 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

