



Fiber Optic Power Reducing Build Out Attenuator, singlemode SC/APC 8°, 2dB, green

- Designed to reduce or balance the power in passive optical networks
- Insertable between the connector and the adapter and therefore suited for distribution frames, cabinets and boxes
- High system flexibility because of wave-length independency and polarization insensitivity

OBSOLETE

This product was discontinued on: July 22, 2020

Replaced By:

C24916-000
OCAB-S2-02-B3

Fiber Optic Power Reducing Build Out Attenuator, singlemode SC/APC 8°, 2dB, green

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber attenuator
Product Series	OCAB

General Specifications

Interface	SC/APC
------------------	--------

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D
Attenuation Tolerance	± 0.5 dB
Attenuation, nominal	2 dB
Operating Wavelength	1260 – 1360 nm
Optical Power, maximum	250 mW
Return Loss, minimum	65 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Storage Temperature -40 °C to +80 °C (-40 °F to +176 °F)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

