158EZNM



Type N Male EZfit® for 1-5/8 in FXL-1873 and AVA7-50 cable

Product Classification

Product TypeWireless and radiating connector

Product Brand EZfit®

Product Series AVA7-50 | AVA7RK-50

Ordering Note ANDREW® non-standard product

General Specifications

Body Style Straight

Inner Contact Attachment Method Captivated

Inner Contact Plating Silver

Interface N Male

Mounting Angle Straight

Outer Contact Attachment Method Clamp

Outer Contact Plating Trimetal

Pressurizable No

Dimensions


Length 76.2 mm | 3 in

Diameter 62.99 mm | 2.48 in

Nominal Size 1-5/8 in

Outline Drawing





Electrical Specifications

3rd Order IMD at Frequency-116 dBm @ 1800 MHz3rd Order IMD Test MethodTwo +43 dBm carriers

Insertion Loss Coefficient, typical 0.05

Average Power at Frequency 0.6 kW @ 900 MHz

Cable Impedance 50 ohm **Connector Impedance** 50 ohm 2000 V dc Test Voltage Inner Contact Resistance, maximum 2 m0hm Insulation Resistance, minimum 5000 MOhm **Operating Frequency Band** 0 - 2700 MHz **Outer Contact Resistance, maximum** 0.3 m0hm Peak Power, maximum 10 kW RF Operating Voltage, maximum (vrms) 707 V

VSWR/Return Loss

Shielding Effectiveness

Frequency Band VSWR Return Loss (dB)

45–400 MHz 1.01 46.07



-130 dB

158EZNM

401-805 MHz	1.028	37.2
806-960 MHz	1.036	35.05
961-1709 MHz	1.06	30.72
1710-2170 MHz	1.048	32.6
2170-2399 MHz	1.06	30.72
2400-2700 MHz	1.06	30.72

Mechanical Specifications

Attachment Durability 25 cycles

Connector Retention Tensile Force 2,224.11 N | 500 lbf

Connector Retention Torque13.56 N-m | 119.998 in lbCoupling Nut Proof Torque4.52 N-m | 39.997 in lbCoupling Nut Retention Force444.82 N | 100 lbf

Coupling Nut Retention Force Method MIL-C-39012C-3.25, 4.6.22

Insertion Force 66.72 N | 15 lbf

Insertion Force Method MIL-C-39012C-3.12, 4.6.9

Interface Durability 500 cycles

Interface Durability Method IEC 61169-16:9.5

Mechanical Shock Test Method MIL-STD-202F, Method 213B, Test Condition C

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature $20~^{\circ}\text{C} \mid 68~^{\circ}\text{F}$ Average Power, Ambient Temperature $40~^{\circ}\text{C} \mid 104~^{\circ}\text{F}$

Corrosion Test Method MIL-STD-1344A, Method 1001.1, Test Condition A

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Moisture Resistance Test Method MIL-STD-202F, Method 106F

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Mated

Water Jetting Test Method IEC 60529:2001, IP66



158EZNM

Packaging and Weights

Weight, net 550.5 g | 1.214 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

* Footnotes

Insertion Loss Coefficient, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

Immersion Depth Immersion at specified depth for 24 hours

