CA-TNMTM



Type N Male to TNC Male Adapter

Product Classification

Product Type Adapter

General Specifications

Body Style Straight

Inner Contact Plating Gold

Interface N Male

Interface 2 TNC Male

Mounting Angle Straight

Outer Contact Plating Trimetal

Pressurizable No

Dimensions


 Width
 22.35 mm | 0.88 in

 Length
 35.81 mm | 1.41 in

Diameter 22.35 mm | 0.88 in

Outline Drawing





Electrical Specifications

Average Power at Frequency 300.0 W @ 900 MHz

Connector Impedance50 ohmdc Test Voltage1500 VInner Contact Resistance, maximum1.5 mOhmInsulation Resistance, minimum5000 MOhmOperating Frequency Band0 - 6000 MHzOuter Contact Resistance, maximum0.4 mOhmPeak Power, maximum5 kW

VSWR/Return Loss

RF Operating Voltage, maximum (vrms)

Frequency Band	VSWR	Return Loss (dB)
0-3000 MHz	1.042	33.74
3000-6000 MHz	1.1	26.444

500 V

Mechanical Specifications

Coupling Nut Proof Torque1.7 N-m | 15.046 in lbCoupling Nut Proof Torque MethodIEC 61169-17:9.3.6Coupling Nut Retention Force445 N | 100.04 lbf



CA-TNMTM

Coupling Nut Retention Force MethodIEC 61169-17:9.3.11Insertion Force28 N | 6.295 lbf

Insertion Force Method IEC 61169-17:9.3.5

Interface Durability 500 cycles

Interface Durability Method IEC 61169-16:9.5 | IEC 61169-17:9.5

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-55 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ (-67 $^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-65 \,^{\circ}\text{C}$ to $+125 \,^{\circ}\text{C}$ (-85 $^{\circ}\text{F}$ to $+257 \,^{\circ}\text{F}$)

Attenuation, Ambient Temperature20 °C | 68 °FAverage Power, Ambient Temperature40 °C | 104 °FAverage Power, Inner Conductor Temperature100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Immersion Depth1 mImmersion Test MatingMated

Immersion Test Method IEC 60529:2001, IP68

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Weight, net 46.06 g | 0.102 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted





CA-TNMTM

* Footnotes

Immersion Depth Immersion at specified depth for 24 hours

