


FGS-MSHS-STOR-F



FiberGuide® Slack Storage Straight Section, 4x12in, Yellow

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Solid straight with slack storage |
| Product Brand | FiberGuide® |
| Product Series | FGS |

General Specifications

| | |
|------------------------|----------------------|
| Product Feature | Snap-together design |
| Color | Yellow |
| Orientation | Horizontal |
| Section Type | Straight Section |

Dimensions

| | |
|--------------------------|--------------------------------|
| Length | 1829 mm 72.008 in |
| System Dimensions | 102 mm x 305 mm (4 in x 12 in) |

Ordering Tree

FGS-MSHS-STOR-F

| | | | |
|-----|----|------------|----|
| 9 | 10 | 11 | |
| FGS | B | - MSHS - F | 10 |

Section Color

| | | |
|---|-------|--------|
| 9 | empty | yellow |
| | B | black |

Section Length

| | | |
|----|-------|-------|
| 11 | empty | 6 ft |
| | 10 | 10 ft |
| | 12 | 12 ft |

Section Size

| | | |
|----|--------|---|
| 10 | A | 4 x 4 in |
| | B | 4 x 6 in |
| | C | 2 x 2 in |
| | D | 4 x 4 in, slotted duct, 2 in slot spacing |
| | F | 4 x 12 in |
| | F-CF | 4 x 12 in, with center divider |
| | G | 2 x 6 in |
| | H | 4 x 24 in |
| | K | 2 x 4 in, slotted duct, 2 in slot spacing |
| | STOR-B | 4 x 6 in, with slack storage spools |
| | STOR-G | 2 x 6 in, with slack storage spools |
| | STOR-F | 4 x 12 in, with slack storage spools |

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 12 kg | 26.455 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



