


# 884027214/10 | CS44ZB WHT C6A 4/23 U/UTP CPK 305M

---



CS44ZB Category 6A U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1000 ft (305 m) length, CommPak

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable


## General Specifications

<b>Product Number</b>	CS44ZB
<b>ANSI/TIA Category</b>	6A
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	U/UTP (unshielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Jacket Color</b>	White
<b>Pairs, quantity</b>	4
<b>Separator Type</b>	Isolator
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   ISO/IEC 11801 Class EA

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Insulated Conductor</b>	0.864 mm   0.034 in
<b>Diameter Over Jacket, nominal</b>	7.239 mm   0.285 in
<b>Jacket Thickness</b>	1.27 mm   0.05 in
<b>Conductor Gauge, singles</b>	23 AWG

## Cross Section Drawing



## Electrical Specifications

<b>dc Resistance Unbalance, maximum</b>	4 %
<b>dc Resistance, maximum</b>	7.61 ohms/100 m   2.32 ohms/100 ft
<b>Mutual Capacitance at Frequency</b>	6.0 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	66 %
<b>Operating Frequency, maximum</b>	550 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
<b>Segregation Class</b>	c

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL	ELTCTL
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	STD
1	2.1	1.8	74.3	91	72.2	89.2	72.3	89	70.2	87.3	67.8	84.5	64.8	82.5	20	33	40	35
4	3.8	3.5	65.3	83.1	61.5	79.6	63.3	81	59.5	77.5	55.8	72.6	52.8	70.5	23	34.6	40	23
8	5.3	5	60.8	79	55.4	73.9	58.8	76.9	53.4	71.8	49.7	66.6	46.7	64.4	24.5	37.3	40	16.9
10	5.9	5.6	59.3	76.6	53.4	71	57.3	74.7	51.4	69.1	47.8	64.7	44.8	62.5	25	38.4	40	15
16	7.5	7.1	56.2	73.6	48.8	66.5	54.2	71.5	46.8	64.3	43.7	60.6	40.7	58.2	25	39.6	38	10.9
20	8.4	8	54.8	73	46.4	65	52.8	71	44.4	63	41.8	58.6	38.8	56.2	25	38.9	37	9
25	9.4	9	53.3	70.6	44	61.7	51.3	68.8	42	59.8	39.8	56.5	36.8	54.2	24.3	38.7	36	7
31.25	10.5	10.1	51.9	68.7	41.4	58.7	49.9	66.9	39.4	56.8	37.9	54.4	34.9	52.1	23.6	39.3	35.1	
62.5	15	14.4	47.4	64.6	32.4	50.3	45.4	62.7	30.4	48.3	31.9	48.5	28.9	46	21.5	36.3	32	
100	19.1	18.4	44.3	60.2	25.2	41.9	42.3	58.7	23.2	40.4	27.8	44.5	24.8	42.2	20.1	35.8	30	
155	24.1	23.2	41.4	60.8	17.4	37.7	39.4	58.8	15.4	35.6	24	41	21	38.7	18.8	33.1	28.1	
200	27.6	26.5	39.8	56.8	12.2	30.4	37.8	55	10.2	28.5	21.8	38.5	18.8	36.3	18	33	27	
250	31.1	29.8	38.3	54.8	7.3	25.1	36.3	52.8	5.3	23	19.8	36.5	16.8	34.2	17.3	32.6	26	
300	34.3	32.9	37.1	53.4	2.9	20.5	35.1	51.4	0.9	18.5	18.3	35	15.3	32.5	16.8	32.5	25.2	
350	37.2	35.7	36.1	52.1	-1.1	16.4	34.1	50.1	-3.1	14.4	16.9	34	13.9	31.4	16.3	33.2	24.6	
400	40.1	38.2	35.3	50.4	-4.8	12.2	33.3	48.3	-6.8	10.1	15.8	32	12.8	30	15.9	34.2	24	
500	45.3	43.1	33.8	47.3	-11.4	4.2	31.8	45.5	-13.4	2.4	13.8	29.9	10.8	27.8	15.2	34.6	23	

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Separator Material</b>	Polyolefin
<b>Separator 2 Material</b>	Polyolefin

## Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

## Environmental Specifications

# 884027214/10 | CS44ZB WHT C6A 4/23 U/UTP CPK 305M

<b>Installation temperature</b>	0 °C to +60 °C (+32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Acid Gas Test Method</b>	EN 50267-2-3
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	B2ca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Smoke Test Method</b>	IEC 61034-2

## Packaging and Weights

<b>Cable weight</b>	55.955 kg/km   37.6 lb/kft
<b>Packaging Type</b>	CommPak® box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

