


# 884033104/10 | CS24R WHT C5E 4/24 F/UTP RL 1KFT

---

Category 5e F/UTP Cable, non-plenum, white jacket, 4 pair count, 1000 ft (305 m) length, reel



## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Twisted pair cable


## General Specifications

<b>Product Number</b>	CS24R
<b>ANSI/TIA Category</b>	5e
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	F/UTP (shielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Drain Wire Type</b>	Solid
<b>Jacket Color</b>	White
<b>Note</b>	All electrical transmission tests include swept frequency measurements
<b>Pairs, quantity</b>	4
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   CENELEC EN 50288-3-1   ISO/IEC 11801 Class D

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Jacket, nominal</b>	6.147 mm   0.242 in
<b>Jacket Thickness</b>	0.508 mm   0.02 in
<b>Conductor Gauge, singles</b>	24 AWG
<b>Drain Wire Gauge</b>	26 AWG

## Cross Section Drawing



## Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>dc Resistance Unbalance, maximum</b>	5 %
<b>dc Resistance, maximum</b>	9.38 ohms/100 m   2.859 ohms/100 ft
<b>Delay Skew, maximum</b>	15 ns
<b>Dielectric Strength, minimum</b>	1500 Vac   2500 Vdc
<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	69 %
<b>Operating Frequency, maximum</b>	100 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
<b>Safety Voltage Rating</b>	300 V

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2	1.9	65.3	83.1	63.3	81.2	62.3	80.8	60.3	78.9	63.8	84.4	60.8	82.4	20	33
4	4.1	3.7	56.3	73.4	52.2	69.8	53.3	71.3	49.2	67.6	51.8	73.3	48.8	71.4	23	30.6
8	5.8	5.2	51.8	69	46	63.9	48.8	67	43	61.8	45.7	67.4	42.7	65.5	24.5	31.5
10	6.5	5.8	50.3	67.2	43.8	61.4	47.3	65.1	40.8	59.3	43.8	65.4	40.8	63.5	25	32.4
16	8.2	7.4	47.2	64.1	39	56.8	44.2	62	36	54.7	39.7	61.3	36.7	59.4	25	31.8
20	9.3	8.2	45.8	62.6	36.5	54.4	42.8	60.5	33.5	52.2	37.8	59.4	34.8	57.4	25	33
25	10.4	9.2	44.3	60.9	33.9	51.6	41.3	58.8	30.9	49.6	35.8	57.6	32.8	55.5	24.3	33.1
31.25	11.7	10.3	42.9	59.6	31.2	49.2	39.9	57.4	28.2	47.1	33.9	55.6	30.9	53.5	23.6	33.4
62.5	17	14.7	38.4	54.4	21.4	39.8	35.4	52.4	18.4	37.7	27.9	49.5	24.9	47.4	21.5	32.9
100	22	18.6	35.3	51	13.3	32.4	32.3	48.9	10.3	30.2	23.8	45.5	20.8	43.3	20.1	29.9
155		23.4		46.9		23.5		45.1		21.7		41.3		39.3		28
200		26.7		45.1		18.4		43.2		16.5		39.1		37		26
250		29.9		44.8		14.9		42.7		12.8		37.1		35.1		25.1
300		32.9		43		10.1		40.9		8		35.6		33.4		25
350		35.7		41.6		5.9		39.7		3.9		34.1		31.8		25.6

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Drain Wire Material</b>	Tinned copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	PVC
<b>Shield (Tape) Material</b>	Aluminum/Polyester

## Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +60 °C (+32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)

# 884033104/10 | CS24R WHT C5E 4/24 F/UTP RL 1KFT

---

**Environmental Space** Non-plenum  
**Flame Test Method** CMR | NEC Article 800 | UL 1666 | UL 444

## Packaging and Weights

**Cable weight** 40.18 kg/km | 27 lb/kft  
**Packaging Type** Reel

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

