

209800-36B



Self-locking Hanger for 1-1/4 in RADIAX® Radiating cable

OBSOLETE

This product was discontinued on: January 30, 2024

Product Classification

Product Type Hanger kit

General Specifications

Cables per Hanger 1
Color Black
Hanger Type Self locking hanger

Dimensions

Maximum Stack Height 2
Height 59.4 mm | 2.339 in
Width 21.1 mm | 0.831 in
Length 41.9 mm | 1.65 in
Compatible Diameter, maximum 39.5 mm | 1.555 in
Compatible Diameter, minimum 35.5 mm | 1.398 in
Nominal Size 1-1/4 in

Material Specifications

Material Type Polyamide PA12

Mechanical Specifications

Maximum Load 1200 N | 269.771 lbf

Environmental Specifications

209800-36B

Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Flammability Test Method	UL 94-HB
Toxicity Index Test Method	IEC 60754-2
UV Resistance, minimum with no degradation	≥500 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed	11.5 cm 4.528 in
Width, packed	14.5 cm 5.709 in
Length, packed	25 cm 9.843 in
Packaging quantity	50
Weight, gross	1.12 kg 2.469 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power