

24312A



Lace-up Hoisting Grip for HELIAX® 1.75-1.99 in (44.5-50.5 mm) cables and elliptical waveguide 43, 52, and 63

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	685.8 mm 27 in
Leader Length, minimum	304.8 mm 12 in
Compatible Diameter, maximum	50.5 mm 1.988 in
Compatible Diameter, minimum	44.5 mm 1.752 in
Nominal Size	1-5/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	430.913 kg 950 lb
---------------------------	---------------------

24312A

Packaging and Weights

Height, packed	38.1 mm 1.5 in
Width, packed	223.52 mm 8.8 in
Length, packed	238.76 mm 9.4 in
Packaging quantity	1
Weight, gross	0.4 kg 0.882 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

