PLUG-12



Cushion Plugs for 1/2 in corrugated coaxial cable

Product Classification

 Product Type
 Cushion plug

 Product Brand
 HELIAX®

Ordering Note ANDREW® non-standard product

General Specifications

Cable TypeCorrugatedColorBlack

Dimensions

Length 76.2 mm | 3 in

Nominal Size 1/2 in

Material Specifications

Material Type EPDM rubber

Environmental Specifications

UV Resistance Test Method MIL-STD-810E, Procedure 11, Method 505

UV Resistance, minimum with no degradation ≥1000 hours

Weather Resistance Test Method 04AS00-03.9.0 | IEC 60529:2001, IP66

Packaging and Weights

 Height, packed
 304.8 mm | 12 in

 Width, packed
 279.4 mm | 11 in

 Length, packed
 25.4 mm | 1 in

Included Five plugs

Packaging quantity 5

Weight, gross 0.06 kg | 0.132 lb

ANDREW® an Amphenol company

PLUG-12

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant