


810009853/DB | C-008-CN-8W-M08YL/28D/D



Fiber indoor/outdoor cable, LightScope® ZWP, dry loose tube, 8 fiber, Singlemode G.652.D and G.657.A1, Gel-free, Yellow jacket color, Dca flame rating

**OBSOLETE**  
This product was discontinued on: March 31, 2023

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-CN


General Specifications

Cable Type	Loose tube
Subunit Type	Gel-free
Jacket Color	Yellow
Jacket Marking	Meters
Fibers per Subunit, quantity	8
Total Fiber Count	8

Dimensions

Cable Length	2000 m   6,561.68 ft
Diameter Over Jacket	6.4 mm   0.252 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	139.7 mm   5.5 in
Minimum Bend Radius, unloaded	129.5 mm   5.098 in
Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	500 N   112.405 lbf

Optical Specifications

Fiber Type	OS2
------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.35 dB/km @ 1,300 nm   0.35 dB/km @ 1,550 nm   0.45 dB/km @ 1,310 nm
Standards Compliance	IEC 60794-1   TIA-492CAAB (OS2)

Environmental Specifications

Installation temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2

810009853/DB | C-008-CN-8W-M08YL/28D/D

---

EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Universal Low Smoke Zero Halogen (ULSZH)

Packaging and Weights

Cable weight	31 kg/km   20.831 lb/kft
--------------	--------------------------

Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber  
8W-250um

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable