SG12-12B2U





Product Classification

Product TypeGrounding kitProduct BrandSureGround®

Ordering Note CommScope® standard product in the United States and Canada

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Smoothwall

Color Black

Grounding Kit Type SureGround® Grounding Kits

Grounding Strap MaterialTinned copperLug AttachmentField attachedLug TypeTwo-hole lug

Thread Size 3/8 in

Dimensions

Bonding Conductor Length1,219.2 mm | 48 inCable Jacketing Removal Length, maximum38.1 mm | 1.5 inCable Jacketing Removal Length, minimum38.1 mm | 1.5 inCompatible Diameter, maximum16.51 mm | 0.65 inCompatible Diameter, minimum15.494 mm | 0.61 in

Nominal Size 1/2 in



SG12-12B2U

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

Lightning Protection Test MethodIEC 1024-1

Material Specifications

Locking Bail MaterialStainless steelRivet MaterialTinned copper

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Blowing Rain Test MethodMIL-STD-810, Method 506Corrosion Test MethodMIL-STD-1344, Method 1001Freezing Rain/Icing Test MethodMIL-STD-810, Method 521

Immersion Test Method IEC 60529:2001, IP68

UV Resistance Test MethodMIL-STD-810, Method 505Vibration Test MethodMIL-STD-202, Method 214Weatherproofing MethodButyl and electric tape

Packaging and Weights

Humidity Test Method

 Height, packed
 447.04 mm | 17.6 in

 Width, packed
 396.24 mm | 15.6 in

 Length, packed
 177.8 mm | 7 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

MIL-STD-1344, Method 1002

Packaging quantity 1

Weight, gross 0.59 kg | 1.301 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

SG12-12B2U

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test MethodProtection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

