

MLOC-5-F1BXMHM-5M



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 male, size 1/4", length 5 meters, covered by conduit shield

OBSOLETE

Product Classification

Product Type	HELIAX® MLOC cluster, SureFlex® Premium, static PIM
Product Brand	HELIAX® SureFlex®
Product Series	MLOC

General Specifications

Attachment, Connector A	Factory attached
Attachment, Connector B	Factory attached
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	M-LOC Male
Interface, Connector B	4.3-10 Male
Specification Sheet Revision Level	A

Dimensions

Length	5 m 16.404 ft
Nominal Size	1/4 in

Electrical Specifications

3rd Order IMD Static	-119 dBm
3rd Order IMD Static Test Method	Two +43 dBm carriers

VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)	Insertion Loss, typical (dB)
1000–3000 MHz	1.07	30	1.89
3000–4200 MHz	1.11	26	2.28

MLOC-5-F1BXMHM-5M

4200–5000 MHz

1.12

25

2.51

Mechanical Specifications

Minimum Bend Radius, multiple Bends 25.4 mm | 1 in

Minimum Bend Radius, single Bend 25.4 mm | 1 in

Environmental Specifications

Installation temperature -40 °C to +60 °C (-40 °F to +140 °F)

Operating Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Immersion Test Method Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



Included Products

FSJ1-50A

– FSJ1-50A, HELIAX® Superflexible Low Density Foam Coaxial Cable, corrugated copper, 1/4 in, black PE jacket