UHXQXQXQF



Ultra Low Loss (ULL) OM4 MPO8 QSFP (Pinned) to MPO8 QSFP (Pinned), Armored Fiber Trunk Cable Assembly, 24-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Color, boot AGrayColor, boot BGrayColor, connector AAquaColor, connector BAqua

Construction Type Stranded | Ultra Low Loss (ULL) armored trunk/extension/cross-connect, indoor

Fibers per Subunit, quantity 8

Furcation Color Aqua

Interface, Connector AMPO-08/UPC MaleInterface Feature, connector AQSFP configurationInterface, Connector BMPO-08/UPC MaleInterface Feature, connector BQSFP configuration

Jacket Color Aqua

Polarity Method B Enhanced (ULL)

Total Fibers, quantity 24



UHXQXQXQF


Dimensions

Breakout Length 33 in

Cable Assembly Length Range (m) 3 - 999

Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 \degree + 4.40 \text{ lb} @ 90 \degree$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, LazrSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Environmental Space Plenum

Included Products

P-024-MZ-5K-F12AQ


760119818 – LazrSPEED® Plenum MPO Trunk Cable, interlocking aluminum armored with plenum jacket, 24

fiber with 12 fiber subunits

860633308 - MPO8, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3m



760119818 | P-024-MZ-5K-F12AQ



LazrSPEED® Plenum MPO Trunk Cable, interlocking aluminum armored with plenum jacket, 24 fiber with 12 fiber subunits

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

Feet

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MZ

General Specifications

Armor Type Interlocking aluminum

Cable Type MPO trunk cable

Construction Type Armored

Fiber Type, quantity 24

Fibers per Subunit, quantity 12

Jacket Color Aqua

Subunit Type Gel-free

Subunit, quantity 2

Total Fiber Count 24

Dimensions

Jacket Marking

Buffer Tube/Subunit Diameter 3 mm | 0.118 in


Diameter Over Armor 15.88 mm | 0.625 in

Diameter Over Jacket 17.9 mm | 0.705 in

Representative Image



760119818 | P-024-MZ-5K-F12AQ



Mechanical Specifications

Minimum Bend Radius, loaded269 mm10.591 inMinimum Bend Radius, unloaded179 mm7.047 inTensile Load, long term, maximum400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

Compression 85 N/mm | 485.363 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 160 m | 524.934 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

COMMSCOPE®

760119818 | P-024-MZ-5K-F12AQ

Operating Temperature 0 °C to +70 °C (+32 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFCP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend 0 °C to +70 °C (+32 °F to +158 °F)

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 256 kg/km | 172.024 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



860633308

MPO8, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3m

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorAquaColor, bootGrayFerrule GeometryFlat

InterfaceMPO MaleInterface FeatureStandard

Total Fiber Count 8

Dimensions

 Length
 60.1 mm | 2.366 in

 Compatible Cable Diameter
 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber ModeMultimodeFiber TypeOM3 | OM4

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

COMMSCOPE®

860633308

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

