

HF210-4SVHS



HELIAX® Hybrid Cable Assembly, 2 power conductors 10 AWG, 4 single mode fibers, DLC to DLC

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	HFT

General Specifications


Conductors, quantity	2
Construction Type	Hybrid standard tail
Interface, Connector A	DLC
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	4

Dimensions

Cable Assembly Length Range (ft)	3 – 400
Diameter Over Jacket	18.31 mm 0.721 in
Center Conductor Gauge	10 AWG

Ordering Tree

HF210-4SVHS



Mechanical Specifications

Minimum Bend Radius 221 mm | 8.701 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2

Insertion Loss, typical note Insertion loss is measured at 1310 and 1550 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

HF210-4SVHS

Cable weight 0.322 kg/m | 0.216 lb/ft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)