



Nylon Cable Tie, 14.25 in length

Product Classification

Product Type	Cable tie
Product Brand	HELIAX®
Ordering Note	ANDREW® standard product (Global)

General Specifications

Color	Black
Hanger Type	Cable tie
Harmonized System (HS) Code	85366910 (Coaxial cable and other coaxial electric conductors)
Mounting	Angle member Cable ladder Round member

Dimensions

Height	1.778 mm 0.07 in
Width	4.572 mm 0.18 in
Length	0.36 m 1.18 ft
Compatible Diameter, maximum	16.764 mm 0.66 in
Compatible Diameter, minimum	10.414 mm 0.41 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Tensile Force	222.411 N 50 lbf
----------------------	--------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

Packaging and Weights

40417

Width, packed	12.2 cm 4.803 in
Length, packed	37.8 cm 14.882 in
Packaging quantity	50
Weight, gross	0.35 kg 0.772 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system