

Fiber OSP cable, PE, Gel-filled Central Tube, 2-fiber, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-CN


## General Specifications

<b>Cable Type</b>	Central loose tube
<b>Construction Type</b>	Non-armored
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Fibers per Subunit, quantity</b>	2
<b>Total Fiber Count</b>	2

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	2.8 mm   0.11 in
<b>Diameter Over Jacket</b>	6 mm   0.236 in

## Representative Image



## Material Specifications

**Jacket Material** PE

## Mechanical Specifications

**Minimum Bend Radius, loaded** 120 mm | 4.724 in  
**Minimum Bend Radius, unloaded** 60 mm | 2.362 in  
**Tensile Load, long term, maximum** 300 N | 67.443 lbf  
**Tensile Load, short term, maximum** 1000 N | 224.809 lbf  
**Compression** 15 N/mm | 85.652 lb/in  
**Compression Test Method** IEC 60794-1-2 E3  
**Flex** 25 cycles  
**Strain** See long and short term tensile loads  
**Strain Test Method** IEC 60794-1-2-E1

## Optical Specifications

**Fiber Type** G.652.D and G.657.A1 | OS2

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.22 dB/km @ 1,550 nm | 0.38 dB/km @ 1,310 nm

## Environmental Specifications

**Installation temperature** -10 °C to +60 °C (+14 °F to +140 °F)

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Buried   Ducted   Outdoor
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5C

## Environmental Test Specifications

<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-2 F1

## Packaging and Weights

<b>Cable weight</b>	35 kg/km   23.519 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable