ConQuest® Empty Conduit, 12.7 mm, black

• *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Hydrostatic Design Basis

Regional Availability	North America
Product Type	Empty conduit
Product Brand	ConQuest®
Government Requirements	Build America Buy America (BABA) compliant*
General Specifications	
Color	Black
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Location of Manufacturing	Catawba, North Carolina
Wall Type	Smooth
Dimensions	
Inner Diameter, nominal	10.008 mm 0.394 in
Outer Diameter, nominal	12.7 mm 0.5 in
Wall Thickness, minimum	1.346 mm 0.053 in
Nominal Size	12.7 mm
Material Specifications	
Flexural Modulus, minimum	551.581 N/mm² 80000 psi
Flexural Property Test Method	ASTM D790

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 1, 2024

Not pressure rated



36000013

Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported	152.4 mm 6 in
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	20.684 N/mm² 3000 psi
Pulling Tension, maximum	86.183 kg 190 lb

Environmental Specifications

Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net

46.133 kg/km | 31 lb/kft

Regulatory Compliance/Certifications

AgencyClassificationISO 9001:2015Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR-Environmental Stress Crack Resistence

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 1, 2024

