


CC9014-000 | OCC1C-X-570-NNNQF



OCC1C CWDM, double mux/demux, 1571 nm starting wavelength, 0.250 mm cable, field installable

OBSOLETE

This product was discontinued on: July 25, 2023

Replaced By:

CP5779-000 OCC1C CWDM, double mux/demux, 1571 nm starting wavelength, 0.250 mm cable, field
OCC1C-X-570-NNNQF-US26 installable

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	CWDM component
Product Series	OCC1C

General Specifications

Device Type	Component, rectangular
Functionality	Multiplexing
Technology Type	Thin film filter (TFF)
Application	For use in FOSC closures
Circuits, quantity	2
Distribution Type	2-channel CWDM
Interface, Input	Stub tail
Interface, Output	Stub tail
Multiplexers, quantity	2

Dimensions

Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter	0.25 mm 0.01 in

Optical Specifications

CC9014-000 | OCC1C-X-570-NNNQF

Starting Wavelength 1571 nm

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

