### NG4-CMD70HS



# NG4access® Cabled Module, singlemode SC/UPC to stub, 144 fiber, ribbon, IFC

- Cabled modules enable the routing of fiber cable to the frame, where multiple connectors are terminated to the frame with a single click
- Integrated connectors ensure the cables are kept in sequential order, and help prevent accidental fiber breakage or disruption to adjacent fibers during installation
- Available in a pigtail version for splicing on frame or preterminated to 24-fiber microcable or conventional IFC cable

#### Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cabled module
Product Brand	NG4access®
Product Series	NG4
Ordering Note	For fiber modules with custom cable lengths, please contact your local CommScope representative

#### **General Specifications**

Configuration Type	NG4 Module to Stub tail
Adapters, quantity, front	144
Body Style	Straight orientation
Cable Color	Yellow
Cable Type	IFC - Ribbon
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	SC/UPC
Interface, rear	Stub tail
Polarity	Pairs, straight
Total Fibers, quantity	144
Total Ports, quantity, front	144

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2023




## NG4-CMD70HS

#### Dimensions

Height	13.3 mm   0.524 in
Width	159.9 mm   6.295 in
Depth	101 mm   3.976 in

### Ordering Tree



#### **Optical Specifications**

Fiber Mode	Singlemode
Fiber Type	G.657.A2

#### **Environmental Specifications**

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 85%, non-condensing

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2023



## NG4-CMD70HS

#### Packaging and Weights

#### Packaging quantity

#### Regulatory Compliance/Certifications

Agency
CHINA-ROHS

**REACH-SVHC** 

Classification Above maximum concentration value Compliant as per SVHC revision on www.commscope.com/ProductCompliance

**UK-ROHS** 

ROHS



Compliant/Exempted Compliant/Exempted

1



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 1, 2023

