

# S-2-UW-H-43-16



Ultra Wideband Two-way Low PIM Reactive High Power Splitter, 555–6000 MHz (Additional mounting bracket PN:42396A-17 sold separately)

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Power splitter

## General Specifications

<b>Device Type</b>	Splitter
<b>Application</b>	Indoor/Outdoor
<b>Color</b>	White
<b>Inner Contact Plating</b>	Silver
<b>Interface</b>	4.3-10 Female
<b>Outer Contact Plating</b>	Trimetal

## Dimensions

<b>Height</b>	25 mm   0.984 in
<b>Width</b>	66 mm   2.598 in
<b>Length</b>	269 mm   10.591 in

## Electrical Specifications

<b>3rd Order IMD</b>	-165 dBc
<b>3rd Order IMD Test Method</b>	Two +43 dBm carriers
<b>Insertion Loss at Frequency Band</b>	0.2 dB @ 555–2700 MHz   0.3 dB @ 2700–6000 MHz
<b>Return Loss, minimum</b>	19.1 dB
<b>Average Power, maximum</b>	300 W
<b>Impedance</b>	50 ohm
<b>Operating Frequency Band</b>	555 – 6000 MHz
<b>Peak Power, maximum</b>	3 kW
<b>Power Rating, Splitting</b>	300 W
<b>Reflected Power, maximum</b>	300 W

# S-2-UW-H-43-16

---

<b>Split Loss</b>	3 dB
<b>VSWR</b>	1.25

## Mechanical Specifications

<b>Coupling Nut Proof Torque</b>	7 N·m   61.955 in lb
----------------------------------	----------------------

## Environmental Specifications

<b>Operating Temperature</b>	-25 °C to +85 °C (-13 °F to +185 °F)
<b>Relative Humidity</b>	Up to 100%
<b>Corrosion Test Method</b>	IEC 60068-2-11, 30 days
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Packaging and Weights

<b>Height, packed</b>	42 mm   1.654 in
<b>Width, packed</b>	77 mm   3.031 in
<b>Length, packed</b>	315 mm   12.402 in
<b>Weight, gross</b>	0.5 kg   1.102 lb
<b>Weight, net</b>	0.42 kg   0.926 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

