



7/8 in EIA Female Flange without gas barrier for 2-1/4 in HJ12-50 air dielectric cable

OBSOLETE

Product Classification

Product Type	Air coaxial connector
Product Brand	HELIAX®

General Specifications

Body Style	Straight
Cable Family	HJ12-50
Gas Barrier	No
Inner Contact Attachment Method	Thread-in stub
Inner Contact Plating	Unplated
Interface	7/8 in EIA Female Flange
Mounting Angle	Straight
Outer Contact Attachment Method	Tab-flare
Outer Contact Plating	Unplated

Dimensions

Length	144.272 mm 5.68 in
Diameter	70.612 mm 2.78 in
Nominal Size	2-1/4 in

Electrical Specifications

Insertion Loss, typical	0.05 dB
Average Power at Frequency	3.5 kW @ 900 MHz

Cable Impedance	50 ohm
Connector Impedance	50 ohm
dc Test Voltage	6 kV
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 2300 MHz
Peak Power, maximum	90 kW
RF Operating Voltage, maximum (vrms)	2121 V

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
0–2200 MHz	1.02	44
2200–3000 MHz	1.03	40

Mechanical Specifications

Interface Durability	50 cycles
Interface Durability Method	MIL-C-39012, Section 4.6.12
Mechanical Shock Test Method	MIL-STD-202, Method 213, Test Condition I

Environmental Specifications

Operating Temperature	-40 °C to +150 °C (-40 °F to +302 °F)
Storage Temperature	-70 °C to +100 °C (-94 °F to +212 °F)
Corrosion Test Method	MIL-STD-202, Method 101, Test Condition B
Moisture Resistance Test Method	MIL-STD-202, Method 106
Thermal Shock Test Method	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
Vibration Test Method	MIL-STD-202, Method 204, Test Condition B

Packaging and Weights

Weight, net	1.6 kg 3.527 lb
--------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Insertion Loss, typical 0.05v⁻freq (GHz) (not applicable for elliptical waveguide)