


CX3199949 | 075G135PP200ROPE-5K' CX



ConQuest® Empty Conduit, 3/4 in, SDR 13.5, gray, with pull rope

Product Classification

Product Type	Empty conduit
Product Brand	ConQuest®

General Specifications

Color	Gray
Conduit Type	Non-toneable
Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³ 0.035 lb/in ³
Density, minimum	0.941 g/cm ³ 0.034 lb/in ³
Design Standard	ASTM D3350-05
Wall Type	Smooth

Dimensions

Length	1524 m 5000 ft
Inner Diameter, nominal	22.2 mm 0.874 in
Outer Diameter, nominal	26.67 mm 1.05 in
Wall Thickness Designation	SDR 13.5
Wall Thickness, minimum	1.981 mm 0.078 in
Nominal Size	3/4 in

Material Specifications

Flexural Modulus, minimum	551.581 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE) Polypropylene
Melt Flow Rate Test Method	ASTM D1238

CX3199949 | 075G135PP200ROPE-5K' CX

Melt Flow Rate, maximum 0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 304.8 mm | 12 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Breaking Strength 90.718 kg | 200 lb

Pull Line Type Rope

Pulling Tension, maximum 229.064 kg | 505 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 165.186 kg/km | 111 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance