100PMR-CR

MCX Male Right Angle for CNT-100 braided cable

Product Classification

Product Type Braided cable connector

Product Brand CNT®

General Specifications

Body Style Right angle

 Inner Contact Attachment Method
 Solder

 Inner Contact Plating
 Gold

Interface MCX Male

Outer Contact Attachment MethodCrimpOuter Contact PlatingGoldPressurizableNo

Dimensions

 Width
 9 mm | 0.354 in

 Length
 10 mm | 0.394 in

 Diameter
 5 mm | 0.197 in

Nominal Size 0.110 in

Electrical Specifications

Insertion Loss, typical 0.05 dB

Average Power at Frequency 50.0 W @ 900 MHz

Cable Impedance50 ohmConnector Impedance50 ohmdc Test Voltage500 VInner Contact Resistance, maximum5 mOhmInsulation Resistance, minimum1000 MOhm

Operating Frequency Band 0 - 6000 MHz

Outer Contact Resistance, maximum 2.5 mOhm

Peak Power, maximum 0.6 kW

RF Operating Voltage, maximum (vrms) 173 V



100PMR-CR

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

0–3000 MHz 1.065 30.05 **3000–6000 MHz** 1.25 19.09

Mechanical Specifications

Connector Retention Tensile Force 98 N | 22.031 lbf

Interface Durability 500 cycles

Mechanical Shock Test Method IEC 60068-2-27

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Storage Temperature -65 °C to +125 °C (-85 °F to +257 °F)

Attenuation, Ambient Temperature $$20\ ^{\circ}\text{C}\ |\ 68\ ^{\circ}\text{F}$$

Average Power, Ambient Temperature 40 $^{\circ}$ C | 104 $^{\circ}$ F

Average Power, Inner Conductor Temperature 100 °C | 212 °F

Climatic Sequence Test Method IEC 60068-1

Corrosion Test Method IEC 60068-2-11

Damp Heat Steady State Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Water Jetting Test Mating Mated

Water Jetting Test Method IEC 60529:2001, IP65

Packaging and Weights

Agency

Weight, net 20 g | 0.044 lb

Regulatory Compliance/Certifications

• •	
CHINA-ROHS	Below maximum concentration value
ICO 0001:201 E	Designed manufactured and/or distribut

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



100PMR-CR



* Footnotes

Insertion Loss, typical 0.05v⁻freq (GHz) (not applicable for elliptical waveguide)

