



AMP-TWIST SL-Series Modular Jack, category 6A, shielded, 4 pair, for FTP cables, side exit, with dust cover

OBSOLETE

This product was discontinued on: September 29, 2020

Replaced By:

2153365-4 AMP-TWIST SLX, 6AS W/DC,GY	AMP-TWIST SLX Series Modular Jack, category 6A, shielded , 4 Pair, with dust cover, gray
760245049 4D-CAP-SLX-50	Four-Direction Cable Exit Cap for SLX Jacks, bag of 50 pcs

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America
Portfolio	NETCONNECT®
Product Type	Modular jack
Product Series	SL Series

General Specifications

ANSI/TIA Category	6A
Cable Type	Shielded
Color	Silver
Conductor Type	Solid Stranded
Integrated Dust Cover Type	Hinged
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Transmission Standards	ANSI/TIA-568-C.2 ISO/IEC 11801 Class EA
Wiring	T568A T568B

1711295-2

Dimensions

Panel Cutout, recommended	14.78 x 20.07 mm (0.58 x 0.79 in)
Panel Thickness, recommended	1.6 mm 0.063 in
Height	20.5 mm 0.807 in
Width	21.5 mm 0.846 in
Depth	36.7 mm 1.445 in
Compatible Cable Diameter, maximum	9 mm 0.354 in
Compatible Insulated Conductor Diameter, maximum	1.6 mm 0.063 in
Contact Plating Thickness	1.27 µm
Compatible Conductor Gauge, solid	24–22 AWG
Compatible Conductor Gauge, stranded	26–24 AWG

Electrical Specifications

PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles
-----------------------	--

Material Specifications

Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Zinc alloy

Mechanical Specifications

Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
-----------------------------------	--------------------------------

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Packaging and Weights

Included	Shutter
Packaging quantity	12
Packaging Type	Tray in box

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

1711295-2

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

