

48 Core OM4 Outdoor Mini Loose Tube - Double Jacket

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LN


General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Blue
Jacket Marking	Meters
Subunit, quantity	6
Fibers per Subunit, quantity	12
Total Fiber Count	48

Dimensions

Buffer Tube/Subunit Diameter	1.55 mm 0.061 in
Diameter Over Jacket	6.3 mm 0.248 in

Representative Image



Material Specifications

Jacket Material Nylon | PE

Mechanical Specifications

Minimum Bend Radius, loaded	160 mm 6.299 in
Minimum Bend Radius, unloaded	65 mm 2.559 in
Tensile Load, short term, maximum	1000 N 224.809 lbf
Compression	20 N/mm 114.203 lb/in
Compression Test Method	IEC 60794-1-21 E3
Flex	25 cycles
Impact	1 N-m 8.851 in lb
Impact Test Method	IEC 60794-1-21 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1-21 E7

Optical Specifications

Fiber Type OM4

Optical Specifications, Wavelength Specific

64624474-48MLT | O-048-LD-5X-M12BL/15G/PE /PA

Attenuation, maximum 0.70 dB/km @ 1,300 nm | 2.50 dB/km @ 850 nm

Environmental Specifications

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature 0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature -20 °C to +70 °C (-4 °F to +158 °F)
Environmental Space Buried | Underground (duct)
Jacket UV Resistance UV stabilized
Water Penetration 24 h
Water Penetration Test Method IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle -10 °C to +60 °C (+14 °F to +140 °F)
Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 33 kg/km | 22.175 lb/kft

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable