

# FA-17MM-114-AD

---



1 1/4 in Double Hanger Kit for HELIAX® Direct Power tails, 17 mm grommet, angle adapter, triple stack, kit of 10

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	184.4 mm   7.26 in
<b>Width</b>	28.7 mm   1.13 in
<b>Length</b>	120.4 mm   4.74 in
<b>Compatible Cable Diameter Range</b>	16–17 mm
<b>Compatible Diameter, maximum</b>	17 mm   0.669 in
<b>Compatible Diameter, minimum</b>	16 mm   0.63 in

## Material Specifications

<b>Material Type</b>	Corrosion proof coated metal   Engineered plastic
----------------------	---

## Mechanical Specifications

<b>Vibration Survival</b>	≥4 hours at resonant frequency
---------------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

# FA-17MM-114-AD

---

<b>Corrosion Resistance, minimum with no degradation</b>	≥500 hours in salt spray chamber
<b>Environmental Strength Capability</b>	Double cable weight
<b>UV Resistance, minimum with no degradation</b>	≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

<b>Packaging quantity</b>	10
---------------------------	----

## Included Products

- DHK-114-6-P – Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter
- HG-58-114 – Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power

# DHK-114-6-P

---



Double Hanger Kit for 1-1/4 in coaxial cable, triple stack; includes hardware and angle adapter

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	ValuSite™
<b>Ordering Note</b>	CommScope® standard product in Europe, the Middle East, and Africa

## General Specifications

<b>Cables per Hanger</b>	6
<b>Color</b>	Black
<b>Hanger Type</b>	Composite clamp
<b>Mounting</b>	M8 hardware

## Dimensions

<b>Maximum Stack Height</b>	3
<b>Height</b>	184.4 mm   7.26 in
<b>Width</b>	25.9 mm   1.02 in
<b>Length</b>	120.4 mm   4.74 in
<b>Compatible Diameter, maximum</b>	40.1 mm   1.579 in
<b>Compatible Diameter, minimum</b>	38.1 mm   1.5 in
<b>Nominal Size</b>	1-1/4 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# DHK-114-6-P

**Material Type** Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 31.8 cm | 12.52 in

**Width, packed** 31.8 cm | 12.52 in

**Length, packed** 7.6 cm | 2.992 in

**Included** Angle adapter | Hardware

**Packaging quantity** 1

**Weight, gross** 0.48 kg | 1.058 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power

# HG-58-114

---



Grommet with 19mm hole for 1-1/4 in SnapStak or polymer block hanger

## Product Classification

<b>Product Type</b>	Grommet
<b>Ordering Note</b>	CommScope® standard product (Global)

## General Specifications

<b>Adapter Type</b>	Adapter
<b>Cables per Hanger</b>	1
<b>Color</b>	Black

## Dimensions

<b>Height</b>	55.626 mm   2.19 in
<b>Diameter Range (cable 1)</b>	19 mm
<b>Nominal Size</b>	1-1/4 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Packaging and Weights

<b>Packaging quantity</b>	10
<b>Weight, gross</b>	0.74 kg   1.631 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant