

iFDT Indoor Fiber Distribution Terminal, 24-fiber, 6 adapters, SC/UPC, soft-wall pigtails, heat shrink splice trays, W/key lock

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

#### **Product Classification**

| Regional Availability | North America               |
|-----------------------|-----------------------------|
| Product Type          | Fiber distribution terminal |
| Product Series        | IFDT                        |

## General Specifications

| Functionality              | Patching   Splicing      |
|----------------------------|--------------------------|
| Adapters, quantity         | 24                       |
| Cable Entry Location       | Bottom right   Top right |
| Cable Type                 | Pigtails - Stranded      |
| Color                      | Putty white              |
| Front Door Type            | Double hinged            |
| Growth Configuration       | Fully loaded             |
| Interface                  | SC/UPC                   |
| Lock Type                  | Padlock ready            |
| Mounting                   | Wall                     |
| Port, quantity             | 24                       |
| Splice Tray Chip Type      | Heat shrink              |
| Splicing Capacity, maximum | 24                       |
|                            |                          |

#### Dimensions

| Height | 203.2 mm   8 in  |
|--------|------------------|
| Width  | 355.6 mm   14 in |
| Depth  | 127 mm   5 in    |


Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

**COMMSCOPE**°

# FDT-BN206NXB000A

# Ordering Tree



#### Material Specifications

| FINISN   |      |
|----------|------|
| Material | Туре |

**F**:--:-I

Powder coated

Steel

### **Optical Specifications**

Fiber Mode

Singlemode

#### **Environmental Specifications**

Environmental Space

**Qualification Standards** 

Indoor

1

NEMA, Type 12 | Telcordia GR-2898-CORE

## Packaging and Weights

Packaging quantity

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

**COMMSCOPE**°

## Regulatory Compliance/Certifications

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Above maximum concentration value                                     |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS       | Compliant/Exempted  |
| UK-ROHS    | Compliant/Exempted  |
| 50         |   |

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

