NGFB-TB1MLU



Next Generation Frame (NGF) Fiber Termination Block with IFC cable, 144 SC/UPC to Stub tail, singlemode, left oriented, upward cable exit, black, 31 meters

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Fiber patch block, with IFC cable

Product Series NGFB

General Specifications

Functionality Patching

Application Used in NGF-style frames only

Body Style Left orientation

Cable Exit LocationUpwardColorBlackColor, frontBlack

Door Type, frontCompression latch | Hinged

Growth ConfigurationFully loadedInterface, frontUnloadedInterface, rearStub tailRack TypeNGFShelf MovementFixed

Total Ports, quantity 144

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications



NGFB-TB1MLU

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

