

NOVUX™ Hardened Indexing Terminal, 12F, 4 Fiber Branching, Dielectric flat loose tube, 100 ft/30 m HMFOC plug (female/no pin) tail

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug and play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ HXT fiber indexing terminals are available with 1:4 or 1:8 splitter and optional multi-use ports, Index Only and Index Branching 2 to 6 fiber solutions
- Available with flat dielectric and flat toneable/locatable dielectric cable
- NOVUX™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

#### Product Classification

Regional Availability

Asia | EMEA | Latin America | North America

**Product Type**Access terminal, without splitter/tap

Product Brand NOVUX™
Product Series HXT

Minimum Order Quantity

General Specifications

Cable TypeDielectric - Flat - Loose Tube

Cable, quantity 1

**Distribution Type** 1 port

**Drop Port Type**Hardened multi-fiber (HMFOC) jack, male/pinned

Drop Port, quantity 1

Enclosure Color Black (RAL 9005)

Forward Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Forward Port, quantity

Mounting Handhole | Pedestal | Pole | Strand

Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Port, quantity 2

Stub Type Hardened multi-fiber (HMFOC) plug, female/no pin

Page 1 of 4

#### **Dimensions**

**Height** 80 mm | 3.15 in


**Width** 95 mm | 3.74 in


**Length** 192 mm | 7.58 in

Cable Length, stub 100 ft (30 m)

**Cable Outer Diameter** 4.3 x 8.0 mm (0.17 x 0.31 in)

### Dimension Drawing






Port Configuration



| NOVUX HT   | TECHNOLOGIES AVAILABLE | SMALL                                   | MEDIUM                 | LARGE                       |
|------------|------------------------|---|------------------------|-----------------------------|
| HXT Series | Fiber indexing         | 12 fiber index only, 1f                 | 12 fiber 1:4           | 12 fiber 1:8                |
|            |                        | 12 fiber index only, 2f                 | 12f multi-use 2f + 1:4 | 12 fiber multi-use, 3f +1:4 |
|            |                        | 12 fiber index only, 3f                 | 24f multi-use 2f       | 12 fiber multi-use, 4f +1:4 |
|            |                        | 12 fiber index only, 4f                 | 24f multi-use 3f       | 12 fiber multi-use, 2f +1:8 |
|            |                        | 12 fiber multi-use, 2f                  | 24f multi-use 4f       |                             |
|            |                        | 12 fiber branching,<br>2 to 6f per port |                        |                             |

#### Ordering Tree



#### Material Specifications

Enclosure Material Type Hardened plastic

**Optical Specifications** 

Fiber Type G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

Attenuation Single Ports, maximum 0.65 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Insertion Loss, Stub Connector, maximum0.65 dBReturn Loss, Connector, typical65 dB

**COMMSCOPE®** 

#### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**UV Resistance** UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Coiled

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

