




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ECR 40153882CMO: REL TO PRODUCTION PER EAO 611325.	23SEP22 PN	MB/JT



NNHH-65C-R2

<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>																																									
TOLERANCES						SAP MATERIAL MASTER																																			
0 PLACE X ±			2 PLACE .XX ±			1 PLACE .X ±			ANGLES ±																																
FINISH						MATERIAL																																			
<b>PRODUCT DRAWING</b>																																									
<table border="1"> <thead> <tr> <th>NAME</th> <th>DATE</th> <th>TITLE</th> </tr> </thead> <tbody> <tr> <td>CE NPHATAK</td> <td>09/23/2022</td> <td rowspan="4" style="text-align: center; vertical-align: middle;"><b>PRODUCT DRAWING</b></td> </tr> <tr> <td>RW NPHATAK</td> <td>09/23/2022</td> </tr> <tr> <td>AD MB1140</td> <td>09/23/2022</td> </tr> <tr> <td>RE RK1070</td> <td>09/23/2022</td> </tr> </tbody> </table>												NAME	DATE	TITLE	CE NPHATAK	09/23/2022	<b>PRODUCT DRAWING</b>	RW NPHATAK	09/23/2022	AD MB1140	09/23/2022	RE RK1070	09/23/2022																		
NAME	DATE	TITLE																																							
CE NPHATAK	09/23/2022	<b>PRODUCT DRAWING</b>																																							
RW NPHATAK	09/23/2022																																								
AD MB1140	09/23/2022																																								
RE RK1070	09/23/2022																																								
<table border="1"> <tr> <td>DENSITY</td> <td>g/mm<sup>3</sup></td> </tr> <tr> <td>MASS</td> <td>grams</td> </tr> <tr> <td>VOLUME</td> <td>mm<sup>3</sup></td> </tr> <tr> <td>SURFACE AREA</td> <td>mm<sup>2</sup></td> </tr> </table>						DENSITY	g/mm <sup>3</sup>	MASS	grams	VOLUME	mm <sup>3</sup>	SURFACE AREA	mm <sup>2</sup>	<table border="1"> <tr> <td>SCALE</td> <td>DOCUMENT NO.</td> </tr> <tr> <td><b>1:5</b></td> <td><b>NNHH-65C-R2-L</b></td> </tr> </table>						SCALE	DOCUMENT NO.	<b>1:5</b>	<b>NNHH-65C-R2-L</b>																		
DENSITY	g/mm <sup>3</sup>																																								
MASS	grams																																								
VOLUME	mm <sup>3</sup>																																								
SURFACE AREA	mm <sup>2</sup>																																								
SCALE	DOCUMENT NO.																																								
<b>1:5</b>	<b>NNHH-65C-R2-L</b>																																								
<table border="1"> <tr> <td>SIZE</td> <td>WORK AREA</td> <td>BSA</td> <td colspan="3">MODEL</td> <td colspan="3">DRAWING</td> <td>SHEET</td> </tr> <tr> <td><b>A2</b></td> <td></td> <td></td> <td>VERSION</td> <td>STATUS</td> <td>REVISION</td> <td>VERSION</td> <td>STATUS</td> <td>REVISION</td> <td>1 OF 1</td> </tr> <tr> <td></td> <td></td> <td></td> <td>00</td> <td>RE</td> <td>A</td> <td>00</td> <td>RE</td> <td>A</td> <td></td> </tr> </table>												SIZE	WORK AREA	BSA	MODEL			DRAWING			SHEET	<b>A2</b>			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1				00	RE	A	00	RE	A	
SIZE	WORK AREA	BSA	MODEL			DRAWING			SHEET																																
<b>A2</b>			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION	1 OF 1																																
			00	RE	A	00	RE	A																																	