


MLOC4-RGXF

Base Product



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with interface type M-LOC female to open end, size 0.141"

Product Classification

Product Type	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
Product Brand	HELIAX® SureFlex®
Product Series	MLOC

General Specifications

Attachment, Connector A	Factory attached
Body Style, Connector A	Straight
Interface, Connector A	M-LOC Female
Specification Sheet Revision Level	A

Dimensions

Nominal Size	0.141 in
---------------------	----------

Electrical Specifications

3rd Order IMD Dynamic Test Method	Two +43 dBm carriers per IEC 62037
--	------------------------------------

Mechanical Specifications

Minimum Bend Radius, multiple Bends	40 mm 1.575 in
Minimum Bend Radius, single Bend	8 mm 0.315 in

Environmental Specifications

Installation temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition