

Fiber outdoor drop cable, LightScope ZWP® Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.A1, 4 fiber Arid Core construction, Gel-filled, central loose tube, Feet jacket marking, Black jacket color, 2000 ft

- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber drop cable
Product Series	O-DF
Government Funding	Build America Buy America (BABA) compliant*

## General Specifications

Cable Type	Central loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Feet
Location of Manufacturing	Catawba, North Carolina
Subunit, quantity	1
Fibers per Subunit, quantity	4
Total Fiber Count	4


## Dimensions

Height Over Jacket	4.5 mm   0.177 in
Cable Length	2000 ft   609.6 m
Buffer Tube/Subunit Diameter	3 mm   0.118 in

810010247/20 | O-004-DF-8W-F04NS (2000')

Diameter Over Jacket7.9 mm | 0.311 in

Representative Image



Material Specifications

Jacket MaterialPE

Mechanical Specifications

Minimum Bend Radius, loaded	86 mm   3.386 in
Minimum Bend Radius, unloaded	81 mm   3.189 in
Tensile Load, long term, maximum	400 N   89.924 lbf
Tensile Load, short term, maximum	1334 N   299.895 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	35 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	2.94 N-m   26.021 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7

Vertical Rise, maximum1047 m | 3,435.039 ft

Optical Specifications

Fiber TypeG.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification StandardsANSI/ICEA S-110-717

Environmental SpaceAerial, self-support | Buried

Jacket UV ResistanceUV stabilized

Water Penetration24 h

Water Penetration Test MethodFOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze-2 °C | 28.4 °F

Cable Freeze Test MethodFOTP-98 | IEC 60794-1 F15

Drip70 °C | 158 °F

Drip Test MethodFOTP-81 | IEC 60794-1 E14

Heat Age-40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test MethodIEC 60794-1 F9

Low High Bend-30 °C to +60 °C (-22 °F to +140 °F)

Low High Bend Test MethodFOTP-37 | IEC 60794-1 E11

Temperature Cycle-40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test MethodFOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight39 kg/km | 26.207 lb/kft

Included Products

DB-8W-LT – LightScope ZWP® Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## LightScope ZWP® Singlemode Fiber



### Product Classification

Portfolio	CommScope®
Product Type	Optical fiber

### General Specifications

Cladding Diameter	125 µm
Cladding Diameter Tolerance	±0.7 µm
Cladding Non-Circularity, maximum	0.7 %
Coating Diameter (Colored)	249 µm
Coating Diameter (Uncolored)	242 µm
Coating Diameter Tolerance (Colored)	±13 µm
Coating Diameter Tolerance (Uncolored)	±5 µm
Coating/Cladding Concentricity Error, maximum	12 µm
Core Diameter	8.3 µm
Core/Clad Offset, maximum	0.5 µm
Proof Test	100000 psi   689.476 N/mm²

### Dimensions

Fiber Curl, minimum	4 m   13.123 ft
---------------------	-----------------

### Mechanical Specifications

Macrobending, 20 mm Ø mandrel, 1 turn	0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm
Macrobending, 30 mm Ø mandrel, 10 turns	0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm
Macrobending, 60 mm Ø mandrel, 100 turns	0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm
Coating Strip Force, maximum	8.9 N   2.001 lbf

# DB-8W-LT

Coating Strip Force, minimum	1.3 N   0.292 lbf
Dynamic Fatigue Parameter, minimum	20

## Optical Specifications

Cabled Cutoff Wavelength, maximum	1260 nm
Point Defects, maximum	0.1 dB
Zero Dispersion Slope, maximum	0.092 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1324 nm
Zero Dispersion Wavelength, minimum	1300 nm

## Optical Specifications, Wavelength Specific

Attenuation, maximum	0.22 dB/km @ 1,550 nm   0.25 dB/km @ 1,490 nm   0.25 dB/km @ 1,625 nm   0.36 dB/km @ 1,310 nm   0.36 dB/km @ 1,385 nm
Attenuation, typical	0.19 dB/km @ 1,550 nm   0.33 dB/km @ 1,310 nm
Backscatter Coefficient	-79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm
Dispersion, maximum	18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
Index of Refraction	1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm
Mode Field Diameter	10.4 µm @ 1,550 nm   9.2 µm @ 1,310 nm   9.6 µm @ 1,385 nm
Mode Field Diameter Tolerance	±0.4 µm @ 1310 nm   ±0.5 µm @ 1550 nm   ±0.6 µm @ 1385 nm
Polarization Mode Dispersion Link Design Value, maximum	0.04 ps/sqrt(km)
Standards Compliance	ITU-T G.652.D   ITU-T G.657.A1

## Environmental Specifications

Heat Aging, maximum	0.05 dB/km @ 85 °C
Temperature Dependence, maximum	0.05 dB/km
Temperature Humidity Cycling, maximum	0.05 dB/km
Water Immersion, maximum	0.05 dB/km @ 23 °C

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# DB-8W-LT

---

\* Footnotes

<b>Temperature Dependence, maximum</b>	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
<b>Temperature Humidity Cycling, maximum</b>	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity