

SRC9-U5A1B1FP000



NOVUX™ Specialty Range Closure 10, splice only, no adapters, no splitters, Ribbon (12F) splice holder, black, tie-wraps & silicon tape (Cable range: 2 - 6.2mm)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

Product Classification

Regional Availability	Asia EMEA Latin America North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC10

General Specifications

Cable Capacity, Drop	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 2 Round 2–6.2 mm (0.08–0.24 in)
Cable Ports Quantity, total	2 round ports
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	In-line
Color	Black
Mounting	Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included
Network Area Type	Drop
Port, quantity	2
Splice Tray Included, quantity	1
Splicing Capacity, Mass Fusion, maximum	12
Splicing Capacity, maximum	4

SRC9-U5A1B1FP000

Splicing Capacity, Single Fusion, maximum	4
Splicing Type, Supported	Single fusion
Splitter Type	No splitter

Dimensions

Width	76 mm 2.992 in
Depth	26 mm 1.024 in
Length	210 mm 8.268 in
Cable Entry Drop Port Diameter	6 mm (0.24 in) mm

Material Specifications

Material Type	Impact-resistant polymer
----------------------	--------------------------

Optical Specifications

Fiber Type	G.657.A1 G.657.A2 G.657.B3
-------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Above ground Below ground Direct burial
Qualification Standards	IEC 60529, IP68 + 1 m waterhead IEC 61753-1, category G
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1
Packaging Type	Box Carton
Weight, net	0.157 kg 0.346 lb